


HOLEX**Flap wheel (A), 80 grit, Head Ø×head width: 50X5mm****Order data**

Order number	554200 50X5
GTIN	4045197803306
Item class	52E

Description**Version:**

Flap strips bonded on to the shank of the tool.

Abrasive strips covered with **Aluminium Oxide (A)**.

Application:

Primarily for finish grinding and polishing tasks on larger radii in tool and mould making, for vessel and machine fabrication. The abrasive strips adapt to the contours of the component.

Technical description

Head Ø	50 mm
Grit	80
maximum speed	16000 min ⁻¹
Head width	5 mm
recommended speed	11000 min ⁻¹
Shank Ø	6 mm

Grinding media	Aluminium Oxide grit (A)
Grinding medium code	A
Product name attribute	80 grit
Type of product	Flap wheel

User data

	Suitability	V_c	ISO code
Alu Mg	suitable		
Steel < 900 N/mm ²	suitable		
Steel < 1400 N/mm ²	suitable only under restricted conditions		
Steel < 55 HRC	suitable		
Steel < 60 HRC	suitable only under restricted conditions		
GG(G)	suitable only under restricted conditions		
CuZn	suitable		
Plastic, GRP	suitable		
Wood	suitable		
dry	suitable		