




Flap wheel (A), 240 grit, Head Ø×head width: 10X10mm



Order data

Order number	554500 10X10
GTIN	4045197803443
Item class	52E

Description

Version:

Flap strips bonded on to the shank of the tool.

Abrasive strips covered with **regular Aluminium Oxide (A)**.

Application:

Primarily for finish grinding and polishing tasks on larger radii in tool and mould making, for vessel and machine fabrication. The abrasive strips adapt to the contours of the component.

Technical description

Head width	10 mm
Grit	240
maximum speed	35000 min ⁻¹
Shank Ø	3 mm
Head Ø	10 mm
recommended speed	26000 min ⁻¹
Grinding media	Aluminium Oxide grit (A)
Grinding medium code	A
Product name attribute	240 grit
Type of product	Flap wheel

User data

	Suitability	V_c	ISO code
Alu Mg	suitable		
Steel < 900 N/mm ²	suitable		
Steel < 1400 N/mm ²	suitable only under restricted conditions		
Steel < 55 HRC	suitable		
Steel < 60 HRC	suitable only under restricted conditions		
GG(G)	suitable only under restricted conditions		
CuZn	suitable		
Plastic, GRP	suitable		
Wood	suitable		
dry	suitable		