



Torque wrench without plug-in head, Maximum torque: 130N·m



Order data

Order number	657215 130
GTIN	4018754268863
Item class	63A

Description

Version:

Sturdy compact one-armed torque wrench, adjustable to scale and self-triggering. The accuracy is sustained for many thousands of operations, because high quality material is used for all wearing parts and the flexible rod is under load only briefly on each occasion. Body and handle are of sturdy square section. Scales adjustable. **Anti-clockwise tightening by reversing the plug-in tools.**

Without any plug-in head (basic model); see No. 657582 – 657950 for suitable plug-in heads.

Units of measure: Nm, lbfft.

Function:

Adjustment: Quick adjustment of the torque with the slide setting button. The value is fixed using the locking key in the handle.

Quick adjustment of the torque with the slide setting button. The value is fixed using the locking key in the handle.

Application:

Since the set torque can be varied, it is ideal for repairs and short series production.

Standard:

Geprüft nach DIN EN ISO 6789.

Cutting dataa:

Legend for drawing and formula:

l_1 = Lever length without plug-in head

l_2 = Adjusted reference dimension on the torque wrench

l_3 = Lever length including factory calibration reference dimension

l_4 = Reference dimension of the plug-in head

L = Total length of the tool

T_1 = Torque to be set

T_2 = Specified torque

Note:

The guaranteed measuring accuracy of the torque is achieved only once the torque range has been calibrated to DIN EN ISO 6789.

Technical description

Torque measuring accuracy	±4 %
Weight	1080 g
maximum torque	130 Nm
Exchangeable tool	Plug-in head
Scale graduation, 1 graduation =	2.5 Nm
Direction of tightening	For right and left-hand tightening
Display	analogue
Socket for plug-in head	14×18 mm
Torque range	25 - 130 Nm
Torque range	20 - 95 lbfft
Adjusted reference dimension on the torque wrench [I ₂]	25 mm
Lever length without plug-in head [I ₁]	390 mm
Connection format	for plug-in heads (rectangular socket)
Trigger principle	mechanical short-travel release
Measurement process	Torque
Standard	DIN EN ISO 6789
Overall length L	410 mm
Lever length including factory calibration reference dimension [I ₃]	415 mm
Adjustable trigger value	adjustable
Setting the trigger value	with adjustment scale
Feedback	triggering
Reversible reading	Nm
Calibration	O1
Test certificate	Manufacturer's test certificate
Data can be recorded	no
Release signalling	akustisk

Release signalling	haptisk
Measurement technology	mechanical
Series	MANOSKOP® 730 Quick
Type of product	Torque Wrench

Services

DAkkS calibrationTorque wrench maximum torque 1000 N·m	020020 1000
CalibrationTorque wrench maximum torque 400 N·m	020010 400

Accessories

Plug-in ratchetwith ejector Type-Square drive 2-1/2 in	657580 2-1/2
Spare handle for torque wrenches Type 4	657211 4
Plug-in ratchet reversible Type-Square drive 2-3/4HD in	657600 2-3/4HD
Plug-in ratchet Square drive 2-1/2 in	657620 2-1/2
Square drive plug-in head Type-Square drive 2-1/2 in	657700 2-1/2
Plug-in ratchet Type-Square drive 2-3/4 in	657630 2-3/4
Plug-in ratchet reversiblewith QuickRelease ejector Type-Square drive 2-1/2 in	657590 2-1/2
Green slide for torque wrench Type 2	657213 2
Plug-in ratchet reversible Type-Square drive 2-3/4 in	657600 2-3/4
Plug-in ratchet reversible Type-Square drive 2-1/2 in	657600 2-1/2
Scale window for torque wrench Type 2	657212 2
Plug-in ratchet reversible Type-Square drive 2-1/2 in	657582 2-1/2
Square drive plug-in head Type-Square drive 2-3/4 in	657700 2-3/4
Plug-in ratchet Type-Square drive 2-1/2 in	657630 2-1/2
Scale window for torque wrench Type 4	657212 4