



Torque wrench without plug-in head, Maximum torque: 400N·m



Order data

Order number	657215 400
GTIN	4018754268887
Item class	63A

Description

Version:

Sturdy compact one-armed torque wrench, adjustable to scale and self-triggering. The accuracy is sustained for many thousands of operations, because high quality material is used for all wearing parts and the flexible rod is under load only briefly on each occasion. Body and handle are of sturdy square section. Scales adjustable. **Anti-clockwise tightening by reversing the plug-in tools.**

Without any plug-in head (basic model); see No. 657582 – 657950 for suitable plug-in heads.

Units of measure: Nm, lbfft.

Function:

Adjustment: Quick adjustment of the torque with the slide setting button. The value is fixed using the locking key in the handle.

Quick adjustment of the torque with the slide setting button. The value is fixed using the locking key in the handle.

Application:

Since the set torque can be varied, it is ideal for repairs and short series production.

Standard:

Tested to DIN EN ISO 6789.

Cutting dataa:

Legend for drawing and formula:

l_1 = Lever length without plug-in head

l_2 = Adjusted reference dimension on the torque wrench

l_3 = Lever length including factory calibration reference dimension

l_4 = Reference dimension of the plug-in head

L = Total length of the tool

T_1 = Torque to be set

T_2 = Specified torque

Note:

The guaranteed measuring accuracy of the torque is achieved only once the torque range has been calibrated to DIN EN ISO 6789.

Technical description

Weight	1620 g
Scale graduation, 1 graduation =	10 Nm
maximum torque	400 Nm
Exchangeable tool	Plug-in head
Direction of tightening	For right and left-hand tightening
Socket for plug-in head	14×18 mm
Display	analogue
Torque measuring accuracy	±4 %
Torque range	80 - 400 Nm
Torque range	60 - 300 lbfft
Lever length without plug-in head [I ₁]	570 mm
Reversible reading	Nm
Overall length L	590 mm
Adjustable trigger value	adjustable
Connection format	for plug-in heads (rectangular socket)
Standard	DIN EN ISO 6789
Feedback	triggering
Lever length including factory calibration reference dimension [I ₃]	595 mm
Adjusted reference dimension on the torque wrench [I ₂]	25 mm
Setting the trigger value	with adjustment scale
Measurement process	Torque
Trigger principle	mechanical short-travel release
Calibration	O1
Test certificate	Manufacturer's test certificate
Data can be recorded	no

Data sheet

Release signalling	akustisk
Release signalling	haptisk
Measurement technology	mechanical
Series	MANOSKOP® 730 Quick
Type of product	Torque Wrench

Suitable products

<https://www.hoffmann-group.com/GB/en/hom/p/657215-400>