



Drill, Type: GBM132RE



Order data

Order number	075420 GBM132RE
GTIN	3165140799737
Item class	03B

Description

Version:

Hand-held power drill with 750-W motor and high torque for holes up to 13 mm in steel.

- **2-speed gearbox.**
- **Ball bearings and anti-friction bearings for precise work and long working life.**
- **Small size of 29 mm across corners.**
- **Stepless speed pre-selection with control wheel.**
- **Control electronics for exact starts to holes.**
- **Overload clutch to protect both user and machine.**
- **Spindle neck Ø 43 mm (Euro standard) – can be used in a drill stand.**
- **Reversible.**
- **Softgrip.**

Advantage:

Holes up to 13 mm Ø in steel.

Supplied with:

Supplied with 13 mm quick-change chuck, additional handle, depth stop 210 mm, L-BOXX 102.

Technical description

Drill chuck adapter	1/2 inch – 20 UNF
maximum twist drill size Ø in wood 1st speed	32 mm
Maximum twist drill size Ø in steel 1st speed	13 mm

maximum speed 2nd speed	3000 min ⁻¹
Weight	2.4 kg
maximum speed 1st speed	1000 min ⁻¹
Chuck clamping range	1.5 - 13 mm
maximum twist drill size Ø in wood 2nd speed	20 mm
maximum vibration to EN	7.5 m/s ²
maximum twist drill size Ø in steel 2nd speed	8 mm
Power consumption	750 W
Manufacturer's designation	GBM 13-2 RE
Power supply	Mains operated
Suitable for material	Steel
Type of product	Drill