



LED machine lamp flat, Type: 546mm



Order data

Order number	081438 546
GTIN	4260131238680
Item class	08C

Description

Version:

Sturdy LED machine lamps in an **aluminium casing**, with a satinised acrylic lens for **homogeneous 160-degree illumination**.

- **Low-reflection, non-dazzle and non-flicker.**
- **For connection to a 24 V mains adapter or 24 V machine control system.**

Flat lighting strip, can pivot through 45°.

Function:

IP67: Protected against intermittent immersion in water and protected against penetration by dust (dust-tight), also completely protected against touching.

Supplied with:

With rubber-clad magnets, mains adapter.

Technical description

Light output	24 W
Illumination	2400 lm
Bulb	LED module

Overall height	36 mm
Power supply	Mains operated
ATEX zone	no
Overall length	546 mm
Overall width	40 mm
IP Index of Protection	IP 67
Type of product	Machine lamp