

HOLEX
**HOLEX Pro Steel solid carbide drill, Weldon shank DIN 6535 HB, TiAlN, Ø DC
h7: 10,4mm**

Order data

Order number	GG1673 10,4
GTIN	4062406207861
Item class	GGN

Description
Version:

Straight major cutting edges and a **special flute profile** ensure good chip evacuation. The robust cutting edge geometry ensures high-performance drilling with good process reliability. A wide range of applications in steel materials thanks to a combination of tough ultra-fine grain carbide and extremely wear-resistant coating.

Same as No. 122777.

Recommendation:
Maximum drilling depth:

Flute length (see table) less 1.5×nominal Ø.

Technical description

Overall length L	118 mm
Flute length L _c	71 mm
Tolerance nominal Ø	h7
Feed f in steel < 900 N/mm ²	0.22 mm/rev.
recommended maximum drilling depth L ₂	55.4 mm
Number of cutting edges Z	2
Nominal Ø D _c	10.4 mm
Shank Ø D _s	12 mm
Standard	DIN 6537
Contents	5

Series	Pro Steel
Coating	TiAlN
Tool material	Solid carbide
Version	6xD
Point angle	140 degrees
Shank	DIN 6535 HB to h6
Through-coolant	yes, with 25 bar
Machining strategy	HPC
Type of product	Jobber drill

User data

	Suitability	V _c	ISO code
Alu plastics	suitable only under restricted conditions	250 m/min	N
Aluminium (short chipping)	suitable only under restricted conditions	200 m/min	N
Alu > 10% Si	suitable only under restricted conditions	160 m/min	N
Steel < 500 N/mm ²	suitable	125 m/min	P
Steel < 750 N/mm ²	suitable	115 m/min	P
Steel < 900 N/mm ²	suitable	95 m/min	P
Steel < 1100 N/mm ²	suitable	90 m/min	P
Steel < 1400 N/mm ²	suitable	65 m/min	P
INOX < 900 N/mm ²	suitable	35 m/min	M
INOX > 900 N/mm ²	suitable only under restricted conditions	30 m/min	M
GG	suitable	100 m/min	K
GGG	suitable	65 m/min	K
wet maximum	suitable		
wet minimum	suitable		

Accessories

HOLEX Pro Steel solid carbide drill, plain shankDIN 6535 HA Ø DC h7 (mm or inch) 10,4	122776 10,4
--	-------------

Shank grinding Type HB	129100 HB
------------------------	-----------