

**HOLEX**
**Solid carbide high performance drill Whistle-Notch shank DIN 6535 HE, TiAlN,  
 Ø DC m7: 16,5mm**

**Order data**

Order number	122398 16,5
GTIN	4045197427267
Item class	12E

**Description**
**Version:**

Cutting chisel edge with **high centring accuracy** due to **strong core and special point geometry**. **Straight major cutting edges** with slightly honed edges and special flute profile produce **short chips**.

**Note:**

Flute length  $L_c = L_2 + 1.5 \times D_c$ .

**Technical description**

Feed $f$ in stainless steel $< 900 \text{ N/mm}^2$	0.16 mm/rev.
Flute length $L_c$	73 mm
Nominal $\varnothing D_c$	16.5 mm
Shank tolerance	h6
Number of cutting edges $Z$	2
Tolerance nominal $\varnothing$	m7
Shank $\varnothing D_s$	18 mm
Overall length $L$	123 mm
Standard	DIN 6537 K
recommended maximum drilling depth $L_2$	48.3 mm
Coating	TiAlN

Tool material	Solid carbide
Version	4xD
Point angle	140 degrees
Shank	DIN 6535 HE to h6
Through-coolant	no
Colour ring	blue
Type of product	Jobber drill

### User data

	Suitability	V <sub>c</sub>	ISO code
Aluminium (short chipping)	suitable only under restricted conditions	140 m/min	N
Alu > 10% Si	suitable only under restricted conditions	120 m/min	N
Steel < 500 N/mm <sup>2</sup>	suitable	80 m/min	P
Steel < 750 N/mm <sup>2</sup>	suitable	75 m/min	P
Steel < 900 N/mm <sup>2</sup>	suitable	65 m/min	P
Steel < 1100 N/mm <sup>2</sup>	suitable only under restricted conditions	60 m/min	P
Steel < 1400 N/mm <sup>2</sup>	suitable only under restricted conditions	35 m/min	P
INOX < 900 N/mm <sup>2</sup>	suitable	35 m/min	M
INOX > 900 N/mm <sup>2</sup>	suitable	30 m/min	M
GG	suitable only under restricted conditions	70 m/min	K
Uni	suitable		
wet maximum	suitable		
wet minimum	suitable only under restricted conditions		

