



## HOLEX Pro Steel solid carbide drill, Weldon shank DIN 6535 HB, TiAlN, Ø DC h7: 3,7mm



### Order data

Order number	GG1673 3,7
GTIN	4062406207823
Item class	GGN

### Description

#### Version:

**Straight major cutting edges** and a **special flute profile** ensure good chip evacuation. The robust cutting edge geometry ensures high-performance drilling with good process reliability. A wide range of applications in steel materials thanks to a combination of tough ultra-fine grain carbide and extremely wear-resistant coating.

Same as No. 122777.

#### Recommendation:

##### Maximum drilling depth:

Flute length (see table) less 1.5×nominal Ø.

### Technical description

Feed f in steel < 900 N/mm <sup>2</sup>	0.11 mm/rev.
Number of cutting edges Z	2
Overall length L	66 mm
Standard	DIN 6537
Tolerance nominal Ø	h7
Flute length L <sub>c</sub>	28 mm
recommended maximum drilling depth L <sub>2</sub>	22.5 mm
Shank Ø D <sub>s</sub>	6 mm
Nominal Ø D <sub>c</sub>	3.7 mm
Contents	5

Series	Pro Steel
Coating	TiAlN
Tool material	Solid carbide
Version	6×D
Point angle	140 degrees
Shank	DIN 6535 HB to h6
Through-coolant	yes, with 25 bar
Machining strategy	HPC
Type of product	Jobber drill

### User data

	Suitability	V <sub>c</sub>	ISO code
Alu plastics	suitable only under restricted conditions	250 m/min	N
Aluminium (short chipping)	suitable only under restricted conditions	200 m/min	N
Alu > 10% Si	suitable only under restricted conditions	160 m/min	N
Steel < 500 N/mm <sup>2</sup>	suitable	125 m/min	P
Steel < 750 N/mm <sup>2</sup>	suitable	115 m/min	P
Steel < 900 N/mm <sup>2</sup>	suitable	95 m/min	P
Steel < 1100 N/mm <sup>2</sup>	suitable	90 m/min	P
Steel < 1400 N/mm <sup>2</sup>	suitable	65 m/min	P
INOX < 900 N/mm <sup>2</sup>	suitable	35 m/min	M
INOX > 900 N/mm <sup>2</sup>	suitable only under restricted conditions	30 m/min	M
GG	suitable	100 m/min	K
GGG	suitable	65 m/min	K
wet maximum	suitable		
wet minimum	suitable		

---

**Accessories**

HOLEX Pro Steel solid carbide drill, plain shankDIN 6535 HA  
Ø DC h7 (mm or inch) 3,7

122776 3,7

Shank grinding Type HB

129100 HB