



## LED hand-held floodlight Spotlight, Type: HS5R



### Order data

Order number	081464 HS5R
GTIN	4013674139828
Item class	04B

### Description

#### Version:

LED hand-held floodlight of ABS plastic with integral rechargeable battery and three LED modules for optimum lighting of the work area.

- **Including attachment magnet for fixing to metallic objects.**
- **Application of a colour filter converts it into a warning light.**
- **2 hours to 9.5 hours of light depending on the light intensity selected.**

#### Function:

IP20: Protected against penetration by foreign bodies with  $\varnothing < 12$  mm, however touching should be avoided, and offers no protection against water.

#### Supplied with:

Lamp, charging station with wall attachment, USB cable, colour filter, operating instructions.

### Technical description

Illumination step 2	105 lm
Illumination time	2 h
Battery voltage	3.7 V
Battery capacity	2.6 Ah
Number of rechargeable batteries contained	1
IP Index of Protection	IP 20

Type of rechargeable battery	Lithium-ion
Illumination	420 lm
Power supply	12
Bulb	LED module
Pivot range	90 degrees
Illumination time stage 2	9.5 h
ATEX zone	no
Type of product	Work lamp