



Torque wrench with plug-in reversible ratchet, Maximum torque: 130N·m



Order data

Order number	657105 130
GTIN	2050002047211
Item class	63A

Description

Version:

Sturdy compact one-armed torque wrench, adjustable to scale and self-triggering. The accuracy is sustained for many thousands of operations, because high quality material is used for all wearing parts and the flexible rod is under load only briefly on each occasion. Body and handle are of sturdy square section. Scales adjustable. **Anti-clockwise tightening by reversing the plug-in tools.**

With **plug-in reversible ratchet**. **Units of measure:** Nm, lbfft.

Function:

Adjustment: Quick adjustment of the torque with the slide setting button. The value is fixed using the locking key in the handle.

Quick adjustment of the torque with the slide setting button. The value is fixed using the locking key in the handle.

Application:

Since the set torque can be varied, it is ideal for repairs and short series production.

Standard:

Geprüft nach DIN EN ISO 6789.

Cutting dataa:

Legend for drawing and formula:

l_1 = Lever length without plug-in head

l_2 = Adjusted reference dimension on the torque wrench

l_3 = Lever length including factory calibration reference dimension

l_4 = Reference dimension of the plug-in head

L = Total length of the tool

T_1 = Torque to be set

T_2 = Specified torque

Note:

The guaranteed measuring accuracy of the torque is achieved only once the torque range has been calibrated to DIN EN ISO 6789.

Technical description

Socket for plug-in head	14×18 mm
Weight	1100 g
Scale graduation, 1 graduation =	2.5 Nm
Direction of tightening	For right and left-hand tightening
Exchangeable tool	Plug-in head
maximum torque	130 Nm
Torque measuring accuracy	±4 %
Square drive	1/2 in
Display	analogue
Torque range	25 - 130 Nm
Torque range	20 - 95 lbfft
Lever length including factory calibration reference dimension [I ₃]	415 mm
Adjusted reference dimension on the torque wrench [I ₂]	25 mm
Adjustable trigger value	adjustable
Feedback	triggering
Standard	DIN EN ISO 6789
Connection format	for plug-in heads (rectangular socket)
Reversible reading	Nm
Trigger principle	mechanical short-travel release
Setting the trigger value	with adjustment scale
Measurement process	Torque
Lever length without plug-in head [I ₁]	390 mm
Calibration	O1
Test certificate	Manufacturer's test certificate
Data can be recorded	no
Release signalling	akustisk

Release signalling	haptisk
Measurement technology	mechanical
Series	MANOSKOP® 730 Quick
Deflection function	no
Slipper function	no
Quick release/ quick-change function	no
Memory pointer	no
Type of product	Torque Wrench

Services

CalibrationTorque wrench maximum torque 400 N·m	020010 400
DAkkS calibrationTorque wrench maximum torque 1000 N·m	020020 1000

Accessories

Plug-in ratchet reversible Type-Square drive 2-3/4HD in	657600 2-3/4HD
Square drive plug-in head Type-Square drive 2-1/2 in	657700 2-1/2
Plug-in ratchet reversible Type-Square drive 2-1/2 in	657582 2-1/2
Scale window for torque wrench Type 2	657212 2
Plug-in ratchetwith ejector Type-Square drive 2-1/2 in	657580 2-1/2
Green slide for torque wrench Type 2	657213 2
Plug-in ratchet reversible Type-Square drive 2-3/4 in	657600 2-3/4
Spare handle for torque wrenches Type 4	657211 4
Square drive plug-in head Type-Square drive 2-3/4 in	657700 2-3/4
Plug-in ratchet Square drive 2-1/2 in	657620 2-1/2
Plug-in ratchet reversiblewith QuickRelease ejector Type-Square drive 2-1/2 in	657590 2-1/2
Plug-in ratchet reversible Type-Square drive 2-1/2 in	657600 2-1/2
Plug-in ratchet Type-Square drive 2-3/4 in	657630 2-3/4

Plug-in ratchet Type-Square drive 2-1/2 in	657630 2-1/2
Torque wrenchwithout plug-in head Maximum torque 130 N·m	657215 130
Scale window for torque wrench Type 4	657212 4