

GARANT Master Tap INOX machine tap HSS-E-PM, TiAIN, UNC: 12-24



Order data

Order number	133356 12-24
GTIN	4062406209544
Item class	111

Description

Version:

High-performance tap, specially developed for **good process reliability** in stainless and acid-resistant steels and duplex materials.

- · HSS-E-PM tool material for maximum wear resistance
- · The latest generation of TiAIN multi-layer coating
- Parameterised flute geometry for optimum chip formation and torsional rigidity Application:

For UNC uniform coarse threads ASME – B1.1.

Thread type: UNC Tool material: HSS E PM

Standard: DIN 371
Threads per inch: 24
Thread Ø: 5.49 mm
Overall length L: 80 mm
Shank Ø D₃: 6 mm

Shank square □: 4.9 mm Tapping hole Ø: 4.5 mm

Technical description

Standard	DIN 371
Thread Ø	5.49 mm
Thread type	UNC
Threads per inch	24
Tool material	HSS E PM

Thread pitch	1.058 mm		
Thread depth	16.47 mm		
Shank square □	4.9 mm		
Overall length L	80 mm		
Number of cutting edges Z	3		
Number of clamping slots	3		
Shank Ø D _s	6 mm		
Thread size	12-24 UNC		
Tapping hole ∅	4.5 mm		
Series	Master Tap		
Coating	TiAlN		
Flank angle	60 °		
Tolerance class	2BX		
Taper lead form	В		
Shank	Plain shank with h9		
Through-coolant	no		
Application for type of drilling	up to 3×D for through holes		
Cutting direction	right-hand		
Type of threading tool	Machine tap for dynamic machining		
Colour ring	blue		
Type of product	Тар		

User data

	Suitability	V _c	ISO code
Aluminium (short chipping)	suitable only under restricted conditions	28 m/min	N
Steel < 750 N/mm ²	suitable only under restricted conditions	23 m/min	Р
Steel < 900 N/mm ²	suitable only under restricted conditions	23 m/min	Р

Steel < 1100 N/mm ²	suitable	12 m/min	Р
INOX < 900 N/mm ²	suitable	11 m/min	М
INOX > 900 N/mm ²	suitable	9 m/min	М
Oil	suitable		
wet maximum	suitable		