

## **GARANT Master Tap INOX machine tap HSS-E-PM, TiAIN, UNC: 7/8-9**



### **Order data**

Order number	133356 7/8-9		
GTIN	4062406209629		
Item class	111		

### **Description**

#### **Version:**

High-performance tap, specially developed for good process reliability in stainless and acid-resistant steels and duplex materials.

- · HSS-E-PM tool material for maximum wear resistance
- · The latest generation of TiAIN multi-layer coating
- · Parameterised flute geometry for optimum chip formation and torsional rigidity **Application:**

**For UNC uniform coarse threads** ASME – B1.1.

Thread type: UNC

Tool material: HSS E PM Standard: DIN 376 Threads per inch: 9 Thread Ø: 22.23 mm Overall length L: 140 mm

Shank Ø D<sub>s</sub>: 18 mm

Shank square □: 14.5 mm Tapping hole Ø: 19.5 mm

## **Technical description**

Tool material	HSS E PM
Number of cutting edges Z	3
Thread pitch	2.822 mm
Shank Ø D <sub>s</sub>	18 mm

Tapping hole Ø	19.5 mm		
Overall length L	140 mm		
Thread size	7/8-9 UNC		
Thread Ø	22.23 mm		
Standard	DIN 376		
Number of clamping slots	3		
Threads per inch	9		
Thread depth	66.69 mm		
Thread type	UNC		
Shank square □	14.5 mm		
Series	Master Tap		
Coating	TiAlN		
Flank angle	60°		
Tolerance class	2BX		
Taper lead form	В		
Shank	Plain shank with h9		
Through-coolant	no		
Application for type of drilling	up to 3×D for through holes		
Cutting direction	right-hand		
Type of threading tool	Machine tap for dynamic machining		
Colour ring	blue		
Type of product	Тар		

# **User data**

	Suitability	$\mathbf{V}_{c}$	ISO code
Aluminium (short chipping)	suitable only under restricted conditions	28 m/min	N
Steel < 750 N/mm <sup>2</sup>	suitable only under restricted conditions	23 m/min	Р

Steel < 900 N/mm <sup>2</sup>	suitable only under restricted conditions	23 m/min	Р
Steel < 1100 N/mm <sup>2</sup>	suitable	12 m/min	Р
INOX < 900 N/mm <sup>2</sup>	suitable	11 m/min	M
INOX > 900 N/mm <sup>2</sup>	suitable	9 m/min	M
Oil	suitable		
wet maximum	suitable		