

Garant

GARANT Master Tap machine tap extra long HSS-E-PM, ALTiX, G: G1/4



Order data

Order number	133333 G1/4
GTIN	4062406208615
Item class	111

Description

Version:

GARANT Master Tap Universal taps, designed for use in a wide spectrum of materials with high process reliability.

- **HSS-E-PM tool material for maximum wear resistance.**
- **Reduced coefficient of friction due to the new high-performance coating.**
- **Special geometry for optimum swarf evacuation.**

With extra-long shank

Advantage:

Ideal for tapping threads in places where access is difficult.

Application:

For Whitworth parallel pipe threads DIN-ISO 228/1 (threads that do not form a seal within the connection).

Tool material: HSS E PM

Threads per inch: 19

Thread Ø: 13.16 mm

Overall length L: 200 mm

Shank Ø D_s: 11 mm

Shank square □: 9 mm

Tapping hole Ø: 11.8 mm

Technical description

Threads per inch	19
Number of cutting edges Z	3
Shank Ø D _s	11 mm
Number of clamping slots	3

Tapping hole Ø	11.8 mm
Tool material	HSS E PM
Thread pitch	1.337 mm
Overall length L	200 mm
Thread size	G1/4
Thread Ø	13.16 mm
Thread depth	39.48 mm
Shank square □	9 mm
Series	Master Tap
Coating	AlTiX
Thread type	G
Flank angle	55°
Standard	Manufacturer's standard
Taper lead form	B
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 3×D for through holes
Cutting direction	right-hand
Type of threading tool	Machine tap for dynamic machining
Colour ring	green
Type of product	Tap

User data

	Suitability	V _c	ISO code
Alu plastics	suitable	24 m/min	N
Aluminium (short chipping)	suitable	28 m/min	N
Alu > 10% Si	suitable	16 m/min	N
Steel < 500 N/mm ²	suitable	24 m/min	P

Steel < 750 N/mm ²	suitable	24 m/min	P
Steel < 900 N/mm ²	suitable	20 m/min	P
Steel < 1100 N/mm ²	suitable	10 m/min	P
Steel < 1400 N/mm ²	suitable	6 m/min	P
INOX < 900 N/mm ²	suitable	8 m/min	M
INOX > 900 N/mm ²	suitable	6 m/min	M
GG(G)	suitable	16 m/min	K
CuZn	suitable	20 m/min	N
Uni	suitable		
Oil	suitable		
wet maximum	suitable		