

Garant
GARANT Master Tap INOX machine tap HSS-E-PM, TiAlN, UNC: 8-32

Order data

Order number	133356 8-32
GTIN	4062406209520
Item class	111

Description
Version:

High-performance tap, specially developed for **good process reliability in stainless and acid-resistant steels** and **duplex materials**.

- **HSS-E-PM tool material for maximum wear resistance**
- **The latest generation of TiAlN multi-layer coating**
- **Parameterised flute geometry for optimum chip formation and torsional rigidity**

Application:

For UNC uniform coarse threads ASME – B1.1.

Thread type: UNC

Tool material: HSS E PM

Standard: DIN 371

Threads per inch: 32

Thread Ø: 4.16 mm

Overall length L: 63 mm

Shank Ø D_s: 4.5 mm

Shank square □: 3.4 mm

Tapping hole Ø: 3.5 mm

Technical description

Thread pitch	0.794 mm
Number of clamping slots	3
Shank Ø D _s	4.5 mm
Number of cutting edges Z	3

Overall length L	63 mm
Thread type	UNC
Standard	DIN 371
Thread depth	12.48 mm
Thread size	8-32 UNC
Thread Ø	4.16 mm
Tool material	HSS E PM
Tapping hole Ø	3.5 mm
Threads per inch	32
Shank square □	3.4 mm
Series	Master Tap
Coating	TiAlN
Flank angle	60 °
Tolerance class	2BX
Taper lead form	B
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 3×D for through holes
Cutting direction	right-hand
Type of threading tool	Machine tap for dynamic machining
Colour ring	blue
Type of product	Tap

User data

	Suitability	V _c	ISO code
Aluminium (short chipping)	suitable only under restricted conditions	28 m/min	N
Steel < 750 N/mm ²	suitable only under restricted conditions	23 m/min	P

Steel < 900 N/mm ²	suitable only under restricted conditions	23 m/min	P
Steel < 1100 N/mm ²	suitable	12 m/min	P
INOX < 900 N/mm ²	suitable	11 m/min	M
INOX > 900 N/mm ²	suitable	9 m/min	M
Oil	suitable		
wet maximum	suitable		