Garant

GARANT Master Tap INOX machine tap HSS-E-PM, TiAIN, UNF: 4-48



Order data

Order number	133406 4-48
GTIN	4062406209643
Item class	111

Description

Version:

High-performance tap, specially developed for good process reliability

in stainless and acid-resistant steels and duplex materials.

- · HSS-E-PM tool material for maximum wear resistance
- · The latest generation of TiAlN multi-layer coating
- $\cdot\,$ Parameterised flute geometry for optimum chip formation and torsional rigidity. Application:

For UNF uniform fine threads ASME – B1.1.

Thread type: UNF Tool material: HSS E PM Standard: DIN 371 Threads per inch: 48 Thread \emptyset : 2.84 mm Overall length L: 56 mm Shank \emptyset D_s: 3.5 mm Shank square \Box : 2.7 mm Tapping hole \emptyset : 2.4 mm

Technical description

Shank square 🗆	2.7 mm
Threads per inch	48
Thread size	4-48 UNF
Thread type	UNF
Thread depth	8.52 mm

© Hoffmann GmbH Qualitätswerkzeuge

Overall length L	56 mm		
Number of clamping slots	3		
Thread Ø	2.84 mm		
Tool material	HSS E PM		
Thread pitch	0.529 mm		
Tapping hole Ø	2.4 mm		
Standard	DIN 371		
Shank Ø D _s	3.5 mm		
Number of cutting edges Z	3		
Series	Master Tap		
Coating	TiAIN		
Flank angle	60 °		
Tolerance class	2BX		
Taper lead form	В		
Shank	Plain shank with h9		
Through-coolant	no		
Application for type of drilling	up to 3×D for through holes		
Cutting direction	right-hand		
Type of threading tool	Machine tap for dynamic machining		
Colour ring	blue		
Type of product	Тар		

User data

	Suitability	V _c	ISO code
Aluminium (short chipping)	suitable only under restricted conditions	28 m/min	Ν
Steel < 750 N/mm ²	suitable only under restricted conditions	23 m/min	Р
Steel < 900 N/mm ²	suitable only under restricted conditions	23 m/min	Р

Steel < 1100 N/mm ²	suitable	12 m/min	Р
INOX < 900 N/mm ²	suitable	11 m/min	М
INOX > 900 N/mm ²	suitable	9 m/min	М
Oil	suitable		
wet maximum	suitable		