Garant

GARANT Master Tap INOX machine tap HSS-E-PM, TiAIN, UNC: 3/4-10

Gerant

Order data

Order number	133356 3/4-10
GTIN	4062406209612
Item class	111

Description

Version:

High-performance tap, specially developed for good process reliability

in stainless and acid-resistant steels and duplex materials.

• HSS-E-PM tool material for maximum wear resistance

· The latest generation of TiAlN multi-layer coating

• Parameterised flute geometry for optimum chip formation and torsional rigidity Application:

For UNC uniform coarse threads ASME – B1.1.

Thread type: UNC Tool material: HSS E PM Standard: DIN 376 Threads per inch: 10 Thread \emptyset : 19.05 mm Overall length L: 125 mm Shank \emptyset D_s: 14 mm Shank square \Box : 11 mm Tapping hole \emptyset : 16.5 mm

Technical description

Thread depth	57.15 mm
Threads per inch	10
Thread pitch	2.54 mm
Tool material	HSS E PM

	DIN 277		
Standard	DIN 376		
Overall length L	125 mm		
Thread type	UNC		
Number of cutting edges Z	3		
Shank square 🗆	11 mm		
Shank Ø D _s	14 mm		
Thread Ø	19.05 mm		
Tapping hole Ø	16.5 mm		
Thread size	3/4-10 UNC		
Number of clamping slots	3		
Series	Master Tap		
Coating	TiAIN		
Flank angle	60 °		
Tolerance class	2BX		
Taper lead form	В		
Shank	Plain shank with h9		
Through-coolant	no		
Application for type of drilling	up to 3×D for through holes		
Cutting direction	right-hand		
Type of threading tool	Machine tap for dynamic machining		
Colour ring	blue		
Type of product	Тар		

User data

	Suitability	V _c	ISO code
Aluminium (short chipping)	suitable only under restricted conditions	28 m/min	Ν
Steel < 750 N/mm²	suitable only under restricted conditions	23 m/min	Ρ

roup 🔥

Data sheet

Steel < 900 N/mm ²	suitable only under restricted conditions	23 m/min	Ρ
Steel < 1100 N/mm ²	suitable	12 m/min	Р
INOX < 900 N/mm ²	suitable	11 m/min	М
INOX > 900 N/mm ²	suitable	9 m/min	М
Oil	suitable		
wet maximum	suitable		