

Garant
GARANT Master Tap INOX machine tap HSS-E-PM Form E, TiAlN, G: G3/4

Order data

Order number	137752 G3/4
GTIN	4062406210342
Item class	111

Description
Version:
GARANT Master Tap INOX:

High-performance tap, specially developed for **good process reliability in stainless and acid-resistant steels** and **duplex materials**.

The 45° helix angle of the chip flutes facilitates chip formation especially in ductile austenitic CrNi steels.

- **HSS-E-PM tool material for maximum wear resistance**
- **The latest generation of TiAlN multi-layer coating**
- **Parameterised flute geometry for optimum chip formation and torsional rigidity**

Form E (1.5-2 turns lead chamfer).

Application:

For Whitworth parallel pipe threads DIN-ISO 228/1 (threads that do not form a seal within the connection).

Tool material: HSS E PM

Threads per inch: 14

Thread Ø: 26.44 mm

Overall length L: 140 mm

Shank Ø D_s: 20 mm

Shank square □: 16 mm

Tapping hole Ø: 24.5 mm

Technical description

Shank square □	16 mm
Number of cutting edges Z	5

Threads per inch	14
Shank $\varnothing D_s$	20 mm
Thread pitch	1.814 mm
Overall length L	140 mm
Tapping hole \varnothing	24.5 mm
Thread \varnothing	26.44 mm
Tool material	HSS E PM
Number of clamping slots	5
Thread depth	66.1 mm
Thread size	G3/4
Series	Master Tap
Coating	TiAlN
Thread type	G
Flank angle	55°
Standard	DIN 5156
Taper lead form	E
Helix angle	45°
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 2.5×D for blind holes
Cutting direction	right-hand
Type of threading tool	Machine tap for dynamic machining
Colour ring	blue
Type of product	Tap

User data

	Suitability	V_c	ISO code
Aluminium (short chipping)	suitable only under restricted conditions	28 m/min	N

Steel < 750 N/mm ²	suitable only under restricted conditions	23 m/min	P
Steel < 900 N/mm ²	suitable only under restricted conditions	23 m/min	P
Steel < 1100 N/mm ²	suitable	12 m/min	P
INOX < 900 N/mm ²	suitable	11 m/min	M
INOX > 900 N/mm ²	suitable	9 m/min	M
Oil	suitable		
wet maximum	suitable		