

**Garant**
**GARANT Master Tap INOX machine tap extra long HSS-E-PM Form B 6HX, TiAlN, M: M16**

**Order data**

Order number	132195 M16
GTIN	4062406209469
Item class	111

**Description**
**Version:**

High-performance tap, specially developed for **good process reliability in stainless and acid-resistant steels** and **duplex materials**.

- **HSS-E-PM tool material for maximum wear resistance**
- **The latest generation of TiAlN multi-layer coating**
- **Parameterised flute geometry for optimum chip formation and torsional rigidity**

**With extra long shank.** Shank to DIN376.

**Advantage:**

Designed for tapping threads where access is difficult.

**Technical description**

Thread type	M
Thread depth	48 mm
Tapping hole Ø	14 mm
Shank Ø D <sub>s</sub>	12 mm
Thread size	M16
Standard	Manufacturer's standard
Number of cutting edges Z	3
Tool material	HSS E PM
Number of clamping slots	3
Thread pitch	2 mm

Shank square <input type="checkbox"/>	9 mm
Thread Ø	16 mm
Overall length L	220 mm
Tolerance class	ISO 2X 6HX
Coating	TiAlN
Flank angle	60 degrees
Thread standard	DIN 13
Taper lead form	B
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 3×D for through holes
Cutting direction	right-hand
Type of threading tool	Machine tap for dynamic machining
Colour ring	blue
Series	Master Tap
Type of product	Tap

## User data

	Suitability	V <sub>c</sub>	ISO code
Aluminium (short chipping)	suitable only under restricted conditions	20 m/min	N
Steel < 750 N/mm <sup>2</sup>	suitable only under restricted conditions	16 m/min	P
Steel < 900 N/mm <sup>2</sup>	suitable only under restricted conditions	16 m/min	P
Steel < 1100 N/mm <sup>2</sup>	suitable	8 m/min	P
INOX < 900 N/mm <sup>2</sup>	suitable	7 m/min	M
INOX > 900 N/mm <sup>2</sup>	suitable	6 m/min	M
Oil	suitable		
wet maximum	suitable		

