

**HOLEX**
**HOLEX Pro Steel solid carbide drill, plain shank DIN 6535 HA, TiAlN, Ø DC h7: 10,4mm**

**Order data**

Order number	GG1672 10,4
GTIN	4062406207786
Item class	GGN

**Description**
**Version:**

**Straight major cutting edges** and a **special flute profile** ensure good chip evacuation. The robust cutting edge geometry ensures high-performance drilling with good process reliability. A wide range of applications in steel materials thanks to a combination of tough ultra-fine grain carbide and extremely wear-resistant coating.

With relieved cone.

**Same as No. 122776.**

Form HB available at the same price, using No. GG1673.

**Note:**

Flute length  $L_c = L_2 + 1.5 \times D_c$ .

**Technical description**

Feed $f$ in steel $< 900 \text{ N/mm}^2$	0.22 mm/rev.
Tolerance nominal $\varnothing$	h7
Number of cutting edges $Z$	2
Shank $\varnothing D_s$	12 mm
recommended maximum drilling depth $L_2$	55.4 mm

Flute length $L_c$	71 mm
Nominal $\varnothing D_c$	10.4 mm
Standard	DIN 6537
Overall length L	118 mm
Contents	5
Series	Pro Steel
Coating	TiAlN
Tool material	Solid carbide
Version	6xD
Point angle	140 degrees
Shank	DIN 6535 HA to h6
Through-coolant	yes, with 25 bar
Machining strategy	HPC
Type of product	Jobber drill

## User data

	Suitability	$V_c$	ISO code
Alu plastics	suitable only under restricted conditions	250 m/min	N
Aluminium (short chipping)	suitable only under restricted conditions	200 m/min	N
Alu > 10% Si	suitable only under restricted conditions	160 m/min	N
Steel < 500 N/mm <sup>2</sup>	suitable	125 m/min	P
Steel < 750 N/mm <sup>2</sup>	suitable	115 m/min	P
Steel < 900 N/mm <sup>2</sup>	suitable	95 m/min	P
Steel < 1100 N/mm <sup>2</sup>	suitable	90 m/min	P
Steel < 1400 N/mm <sup>2</sup>	suitable	65 m/min	P
INOX < 900 N/mm <sup>2</sup>	suitable	35 m/min	M

INOX > 900 N/mm <sup>2</sup>	suitable only under restricted conditions	30 m/min	M
GG	suitable	100 m/min	K
GGG	suitable	65 m/min	K
Uni	suitable		
wet maximum	suitable		
wet minimum	suitable		

## Accessories

HOLEX Pro Steel solid carbide drill, plain shankDIN 6535 HA  
Ø DC h7 (mm or inch) 10,4

122776 10,4