

## **GARANT Master Tap INOX machine tap HSS-E-PM, TiAIN, UNF: 5-44**



### Order data

Order number	138007 5-44
GTIN	4062406210168
Item class	111

## **Description**

#### **Version:**

### **GARANT Master Tap INOX:**

High-performance tap, specially developed for **good process reliability in stainless and acid-resistant steels** and **duplex materials.** 

**The 45° helix angle** of the chip flutes facilitates chip formation especially in ductile austenitic CrNi steels.

- · HSS-E-PM tool material for maximum wear resistance
- The latest generation of TiALN multi-layer coating
- · Parameterised flute geometry for optimum chip formation and torsional rigidity Application:

**For UNF uniform fine threads** ASME – B1.1.

Thread type: UNF

Tool material: HSS E PM Standard: DIN 371 Threads per inch: 44 Thread  $\varnothing$ : 3.17 mm Overall length L: 56 mm Shank  $\varnothing$  D<sub>s</sub>: 3.5 mm Shank square  $\square$ : 2.7 mm Tapping hole  $\varnothing$ : 2.7 mm

# **Technical description**

Threads per inch	44
Standard	DIN 371
Shank square □	2.7 mm

Thread pitch	0.577 mm		
Thread type	UNF		
Tool material	HSS E PM		
Thread Ø	3.17 mm		
Thread size	5-44 UNF		
Thread depth	7.925 mm		
Number of cutting edges Z	3		
Overall length L	56 mm		
Shank Ø D <sub>s</sub>	3.5 mm		
Number of clamping slots	3		
Tapping hole Ø	2.7 mm		
Series	Master Tap		
Coating	TiAlN		
Flank angle	60 °		
Tolerance class	2BX		
Taper lead form	С		
Helix angle	45 °		
Shank	Plain shank with h9		
Through-coolant	no		
Application for type of drilling	up to 2.5×D for blind holes		
Cutting direction	right-hand		
Type of threading tool	Machine tap for dynamic machining		
Colour ring	blue		
Type of product	Тар		

# **User data**

	Suitability	$\mathbf{V}_{c}$	ISO code
Aluminium (short chipping)	suitable only under restricted conditions	28 m/min	N

Steel < 750 N/mm <sup>2</sup>	suitable only under restricted conditions	23 m/min	Р
Steel < 900 N/mm <sup>2</sup>	suitable only under restricted conditions	23 m/min	Р
Steel < 1100 N/mm <sup>2</sup>	suitable	12 m/min	Р
INOX < 900 N/mm <sup>2</sup>	suitable	11 m/min	М
INOX > 900 N/mm <sup>2</sup>	suitable	9 m/min	М
Oil	suitable		
wet maximum	suitable		