

Garant

GARANT Master Tap machine tap for wire thread inserts HSS-E-PM, AlTiX, EG-M: EG-M2,5



Order data

Order number	133560 EG-M2,5
GTIN	4062406208257
Item class	111

Description

Version:

Tap to **DIN 40435 (similar to DIN 371 / DIN 376)**.

GARANT Master Tap Universal taps, designed for use in a wide spectrum of materials with high process reliability.

- **HSS-E-PM tool material for maximum wear resistance.**
- **Reduced coefficient of friction due to the new high-performance coating.**
- **Special geometry for optimum swarf evacuation.**

Application:

For production of EG mounting thread according to metric ISO thread **DIN 8140** for **STI wire thread inserts** (Screw Thread Insert).

Note:

Please ensure without fail the correct **tapping drill Ø** (see table)!

Tool material: HSS E PM

Standard: DIN 40435

Tolerance class: 6HX mod.

Thread pitch: 0.45 mm

Overall length L: 56 mm

Shank Ø D_s: 3.5 mm

Shank square □: 2.7 mm

Tapping hole Ø: 2.65 mm

Technical description

Overall length L	56 mm
Thread size	M2.5

Standard	DIN 40435
Tapping hole \varnothing	2.65 mm
Tolerance class	6HX mod.
Number of cutting edges Z	3
Tool material	HSS E PM
Thread \varnothing	2.5 mm
Shank $\varnothing D_s$	3.5 mm
Thread depth	7.5 mm
Thread pitch	0.45 mm
Number of clamping slots	3
Shank square \square	2.7 mm
Coating	AlTiX
Thread type	EG-M
Flank angle	60°
Taper lead form	B
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 3×D for through holes
Cutting direction	right-hand
Type of threading tool	Machine tap for dynamic machining
Colour ring	green
Series	Master Tap
Type of product	Tap

User data

	Suitability	V_c	ISO code
Alu plastics	suitable	30 m/min	N
Aluminium (short chipping)	suitable	35 m/min	N

Alu > 10% Si	suitable	20 m/min	N
Steel < 500 N/mm ²	suitable	30 m/min	P
Steel < 750 N/mm ²	suitable	30 m/min	P
Steel < 900 N/mm ²	suitable	25 m/min	P
Steel < 1100 N/mm ²	suitable	12 m/min	P
Steel < 1400 N/mm ²	suitable	8 m/min	P
INOX < 900 N/mm ²	suitable	10 m/min	M
INOX > 900 N/mm ²	suitable	8 m/min	M
GG(G)	suitable	20 m/min	K
CuZn	suitable	20 m/min	N
Uni	suitable		
Oil	suitable		
wet maximum	suitable		