

GARANT Master Tap INOX machine tap HSS-E-PM, TiAIN, UNF: 5/16-24



Order data

Order number	133406 5/16-24
GTIN	4062406209711
Item class	111

Description

Version:

High-performance tap, specially developed for **good process reliability**

in stainless and acid-resistant steels and duplex materials.

- · HSS-E-PM tool material for maximum wear resistance
- · The latest generation of TiAIN multi-layer coating
- · Parameterised flute geometry for optimum chip formation and torsional rigidity.

Application:

For UNF uniform fine threads ASME – B1.1.

Thread type: UNF

Tool material: HSS E PM Standard: DIN 371 Threads per inch: 24 Thread Ø: 7.94 mm Overall length L: 90 mm Shank Ø D_s: 8 mm

Shank square \square : 6.2 mm Tapping hole \varnothing : 6.9 mm

Technical description

Thread type	UNF
Tapping hole Ø	6.9 mm
Thread depth	23.82 mm
Thread pitch	1.058 mm

Number of clamping slots	3		
Threads per inch	24		
Thread size	5/16-24 UNF		
Tool material	HSS E PM		
Shank Ø D _s	8 mm		
Number of cutting edges Z	3		
Thread Ø	7.94 mm		
Standard	DIN 371		
Shank square □	6.2 mm		
Overall length L	90 mm		
Series	Master Tap		
Coating	TiAlN		
Flank angle	60 °		
Tolerance class	2BX		
Taper lead form	В		
Shank	Plain shank with h9		
Through-coolant	no		
Application for type of drilling	up to 3×D for through holes		
Cutting direction	right-hand		
Type of threading tool	Machine tap for dynamic machining		
Colour ring	blue		
Type of product	Тар		

User data

	Suitability	\mathbf{V}_{c}	ISO code
Aluminium (short chipping)	suitable only under restricted conditions	28 m/min	N
Steel < 750 N/mm ²	suitable only under restricted conditions	23 m/min	Р

Steel < 900 N/mm ²	suitable only under restricted conditions	23 m/min	Р
Steel < 1100 N/mm ²	suitable	12 m/min	Р
INOX < 900 N/mm ²	suitable	11 m/min	M
INOX > 900 N/mm ²	suitable	9 m/min	M
Oil	suitable		
wet maximum	suitable		