

**Garant**
**GARANT Master Tap INOX machine tap HSS-E-PM, TiAlN, UNF: 5/8-18**

**Order data**

Order number	133406 5/8-18
GTIN	4062406209759
Item class	111

**Description**
**Version:**

High-performance tap, specially developed for **good process reliability in stainless and acid-resistant steels and duplex materials.**

- **HSS-E-PM tool material for maximum wear resistance**
- **The latest generation of TiAlN multi-layer coating**
- **Parameterised flute geometry for optimum chip formation and torsional rigidity.**

**Application:**

**For UNF uniform fine threads ASME – B1.1.**

Thread type: UNF

Tool material: HSS E PM

Standard: DIN 374

Threads per inch: 18

Thread Ø: 15.88 mm

Overall length L: 100 mm

Shank Ø D<sub>s</sub>: 12 mm

Shank square □: 9 mm

Tapping hole Ø: 14.5 mm

**Technical description**

Thread depth	47.64 mm
Thread Ø	15.88 mm
Shank square □	9 mm
Number of cutting edges Z	4

Number of clamping slots	4
Tool material	HSS E PM
Overall length L	100 mm
Threads per inch	18
Thread type	UNF
Thread size	5/8-18 UNF
Standard	DIN 374
Shank $\varnothing D_s$	12 mm
Tapping hole $\varnothing$	14.5 mm
Thread pitch	1.58 mm
Series	Master Tap
Coating	TiAlN
Flank angle	60°
Tolerance class	2BX
Taper lead form	B
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 3×D for through holes
Cutting direction	right-hand
Type of threading tool	Machine tap for dynamic machining
Colour ring	blue
Type of product	Tap

## User data

	Suitability	$V_c$	ISO code
Aluminium (short chipping)	suitable only under restricted conditions	28 m/min	N
Steel < 750 N/mm <sup>2</sup>	suitable only under restricted conditions	23 m/min	P

Steel < 900 N/mm <sup>2</sup>	suitable only under restricted conditions	23 m/min	P
Steel < 1100 N/mm <sup>2</sup>	suitable	12 m/min	P
INOX < 900 N/mm <sup>2</sup>	suitable	11 m/min	M
INOX > 900 N/mm <sup>2</sup>	suitable	9 m/min	M
Oil	suitable		
wet maximum	suitable		