

GARANT Master Tap INOX machine tap HSS-E-PM, TiAIN, UNF: 1/2-20



Order data

Order number	138007 1/2-20
GTIN	4062406210250
Item class	111

Description

Version:

GARANT Master Tap INOX:

High-performance tap, specially developed for **good process reliability in stainless and acid-resistant steels** and **duplex materials.**

The 45° helix angle of the chip flutes facilitates chip formation especially in ductile austenitic CrNi steels.

- · HSS-E-PM tool material for maximum wear resistance
- The latest generation of TiALN multi-layer coating
- Parameterised flute geometry for optimum chip formation and torsional rigidity Application:

For UNF uniform fine threads ASME – B1.1.

Thread type: UNF

Tool material: HSS E PM Standard: DIN 374 Threads per inch: 20 Thread Ø: 12.7 mm

Overall length L: 100 mm

Shank Ø D₅: 9 mm Shank square □: 7 mm Tapping hole Ø: 11.5 mm

Technical description

Thread Ø	12.7 mm
Threads per inch	20

Standard	DIN 374		
Number of cutting edges Z	4		
Thread size	1/2-20 UNF		
Tool material	HSS E PM		
Number of clamping slots	4		
Thread type	UNF		
Tapping hole ∅	11.5 mm		
Shank Ø D _s	9 mm		
Thread depth	31.75 mm		
Overall length L	100 mm		
Shank square □	7 mm		
Thread pitch	1.27 mm		
Series	Master Tap		
Coating	TiAlN		
Flank angle	60 °		
Tolerance class	2BX		
Taper lead form	С		
Helix angle	45 °		
Shank	Plain shank with h9		
Through-coolant	no		
Application for type of drilling	up to 2.5×D for blind holes		
Cutting direction	right-hand		
Type of threading tool	Machine tap for dynamic machining		
Colour ring	blue		
Type of product	Тар		

User data

	Suitability	\mathbf{V}_{c}	ISO code
--	-------------	------------------	----------

Aluminium (short chipping)	suitable only under restricted conditions	28 m/min	N
Steel < 750 N/mm ²	suitable only under restricted conditions	23 m/min	Р
Steel < 900 N/mm ²	suitable only under restricted conditions	23 m/min	Р
Steel < 1100 N/mm ²	suitable	12 m/min	Р
INOX < 900 N/mm ²	suitable	11 m/min	М
INOX > 900 N/mm ²	suitable	9 m/min	М
Oil	suitable		
wet maximum	suitable		