

Garant
GARANT Master Tap INOX machine tap HSS-E-PM Form B 6GX, TiAlN, M: M14

Order data

Order number	132193 M14
GTIN	4062406209353
Item class	111

Description
Version:

High-performance tap, specially developed for **good process reliability in stainless and acid-resistant steels** and **duplex materials**.

- **HSS-E-PM tool material for maximum wear resistance**
- **The latest generation of TiAlN multi-layer coating**
- **Parameterised flute geometry for optimum chip formation and torsional rigidity**

Tolerance class: ISO 3X/6GX. For components which are **galvanised** or shrink slightly when hardened.

Thread type: M

Tool material: HSS E PM

Standard: DIN 376

Tolerance class: ISO 3X 6GX

Thread pitch: 2 mm

Overall length L: 110 mm

Shank \varnothing D_s: 11 mm

Shank square □: 9 mm

Tapping hole \varnothing : 12 mm

Technical description

Number of clamping slots	3
Shank square □	9 mm
Thread \varnothing	14 mm
Thread size	M14
Tool material	HSS E PM

Number of cutting edges Z	3
Standard	DIN 376
Tapping hole Ø	12 mm
Thread pitch	2 mm
Tolerance class	ISO 3X 6GX
Shank Ø D _s	11 mm
Thread type	M
Overall length L	110 mm
Thread depth	42 mm
Coating	TiAlN
Flank angle	60 °
Thread standard	DIN 13
Taper lead form	B
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 3×D for through holes
Cutting direction	right-hand
Type of threading tool	Machine tap for dynamic machining
Colour ring	blue
Series	Master Tap
Type of product	Tap

User data

	Suitability	V _c	ISO code
Aluminium (short chipping)	suitable only under restricted conditions	28 m/min	N
Steel < 750 N/mm ²	suitable only under restricted conditions	23 m/min	P
Steel < 900 N/mm ²	suitable only under restricted conditions	23 m/min	P

Steel < 1100 N/mm ²	suitable	12 m/min	P
INOX < 900 N/mm ²	suitable	11 m/min	M
INOX > 900 N/mm ²	suitable	9 m/min	M
Oil	Suitable		
wet maximum	suitable		