# Garant

## GARANT Master Tap INOX machine tap HSS-E-PM, TiAIN, UNC: 1-8



## Order data

Order number	133356 1-8
GTIN	4062406209636
Item class	111

# Description

#### Version:

High-performance tap, specially developed for good process reliability

in stainless and acid-resistant steels and duplex materials.

- · HSS-E-PM tool material for maximum wear resistance
- · The latest generation of TiAlN multi-layer coating
- $\cdot\,$  Parameterised flute geometry for optimum chip formation and torsional rigidity Application:

For UNC uniform coarse threads ASME – B1.1.

Thread type: UNC Tool material: HSS E PM Standard: DIN 376 Threads per inch: 8 Thread  $\emptyset$ : 25.4 mm Overall length L: 160 mm Shank  $\emptyset$  D<sub>s</sub>: 18 mm Shank square  $\Box$ : 14.5 mm Tapping hole  $\emptyset$ : 22.25 mm

## **Technical description**

Number of cutting edges Z	4
Thread pitch	3.175 mm
Shank square 🗆	14.5 mm
Tool material	HSS E PM
Thread type	UNC

© Hoffmann GmbH Qualitätswerkzeuge

Overall length L	160 mm		
Thread Ø	25.4 mm		
Threads per inch	8		
Thread size	1-8 UNC		
Number of clamping slots	4		
Thread depth	76.2 mm		
Standard	DIN 376		
Tapping hole Ø	22.25 mm		
Shank Ø D <sub>s</sub>	18 mm		
Series	Master Tap		
Coating	TiAIN		
Flank angle	60 °		
Tolerance class	2BX		
Taper lead form	В		
Shank	Plain shank with h9		
Through-coolant	no		
Application for type of drilling	up to 3×D for through holes		
Cutting direction	right-hand		
Type of threading tool	Machine tap for dynamic machining		
Colour ring	blue		
Type of product	Тар		

# User data

	Suitability	V <sub>c</sub>	ISO code
Aluminium (short chipping)	suitable only under restricted conditions	28 m/min	Ν
Steel < 750 N/mm²	suitable only under restricted conditions	23 m/min	Р
Steel < 900 N/mm²	suitable only under restricted conditions	23 m/min	Ρ

Steel < 1100 N/mm <sup>2</sup>	suitable	12 m/min	Р
INOX < 900 N/mm <sup>2</sup>	suitable	11 m/min	М
INOX > 900 N/mm <sup>2</sup>	suitable	9 m/min	М
Oil	suitable		
wet maximum	suitable		