

Garant
GARANT Master Tap INOX machine tap HSS-E-PM Form C 6GX, TiAlN, M: M3

Order data

Order number	135737 M3
GTIN	4062406209797
Item class	111

Description
Version:

High-performance tap, specially developed for **good process reliability in stainless and acid-resistant steels** and **duplex materials**.

The 45° helix angle of the flutes facilitates chip formation especially in ductile austenitic CrNi steels.

- **HSS-E-PM tool material for a high degree of wear resistance**
- **The latest generation of TiAlN multi-layer coating**
- **Parameterised flute geometry for optimum chip formation and torsional rigidity**

Tolerance class ISO 3X/6GX. For components which are **galvanised** or shrink slightly when hardened.

Thread type: M

Tool material: HSS E PM

Standard: DIN 371

Tolerance class: ISO 3X 6GX

Thread pitch: 0.5 mm

Overall length L: 56 mm

Shank $\varnothing D_s$: 3.5 mm

Shank square \square : 2.7 mm

Tapping hole \varnothing : 2.5 mm

Technical description

Thread depth	7.5 mm
Tool material	HSS E PM
Tapping hole \varnothing	2.5 mm
Thread \varnothing	3 mm

Tolerance class	ISO 3X 6GX
Shank square \square	2.7 mm
Thread size	M3
Thread pitch	0.5 mm
Standard	DIN 371
Number of clamping slots	3
Number of cutting edges Z	3
Shank $\varnothing D_s$	3.5 mm
Thread type	M
Overall length L	56 mm
Coating	TiAlN
Flank angle	60°
Thread standard	DIN 13
Taper lead form	C
Helix angle	45°
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 2.5×D for blind holes
Cutting direction	right-hand
Type of threading tool	Machine tap for dynamic machining
Colour ring	blue
Series	Master Tap
Type of product	Tap

User data

	Suitability	V_c	ISO code
Aluminium (short chipping)	suitable only under restricted conditions	28 m/min	N

Steel < 750 N/mm ²	suitable only under restricted conditions	23 m/min	P
Steel < 900 N/mm ²	suitable only under restricted conditions	23 m/min	P
Steel < 1100 N/mm ²	suitable	12 m/min	P
INOX < 900 N/mm ²	suitable	11 m/min	M
INOX > 900 N/mm ²	suitable	9 m/min	M
Oil	suitable		
wet maximum	suitable		