

GARANT Master Tap INOX machine tap HSS-E-PM, TiAIN, UNF: 6-40



Order data

| Order number | 133406 6-40 |
|--------------|---------------|
| GTIN | 4062406209667 |
| Item class | 111 |

Description

Version:

High-performance tap, specially developed for **good process reliability** in stainless and acid-resistant steels and duplex materials.

- · HSS-E-PM tool material for maximum wear resistance
- · The latest generation of TiAIN multi-layer coating
- · Parameterised flute geometry for optimum chip formation and torsional rigidity.

Application:

For UNF uniform fine threads ASME – B1.1.

Thread type: UNF

Tool material: HSS E PM Standard: DIN 371 Threads per inch: 40 Thread Ø: 3.51 mm Overall length L: 56 mm Shank Ø D₅: 4 mm Shank square □: 3 mm Tapping hole Ø: 2.95 mm

Technical description

| Thread type | UNF |
|---------------------------|----------|
| Standard | DIN 371 |
| Number of cutting edges Z | 3 |
| Shank Ø D _s | 4 mm |
| Thread pitch | 0.635 mm |

| Thread size | 6-40 UNF | | |
|----------------------------------|-----------------------------------|--|--|
| Tool material | HSS E PM | | |
| Tapping hole Ø | 2.95 mm | | |
| Overall length L | 56 mm | | |
| Number of clamping slots | 3 | | |
| Thread depth | 10.53 mm | | |
| Shank square □ | 3 mm | | |
| Thread Ø | 3.51 mm | | |
| Threads per inch | 40 | | |
| Series | Master Tap | | |
| Coating | TiAIN | | |
| Flank angle | 60 ° | | |
| Tolerance class | 2BX | | |
| Taper lead form | В | | |
| Shank | Plain shank with h9 | | |
| Through-coolant | no | | |
| Application for type of drilling | up to 3×D for through holes | | |
| Cutting direction | right-hand | | |
| Type of threading tool | Machine tap for dynamic machining | | |
| Colour ring | blue | | |
| Type of product | Тар | | |

User data

| | Suitability | \mathbf{V}_{c} | ISO code |
|-------------------------------|---|------------------|----------|
| Aluminium (short chipping) | suitable only under restricted conditions | 28 m/min | N |
| Steel < 750 N/mm ² | suitable only under restricted conditions | 23 m/min | Р |
| Steel < 900 N/mm ² | suitable only under restricted conditions | 23 m/min | Р |

| Steel < 1100 N/mm ² | suitable | 12 m/min | Р |
|--------------------------------|----------|----------|---|
| INOX < 900 N/mm ² | suitable | 11 m/min | М |
| INOX > 900 N/mm ² | suitable | 9 m/min | М |
| Oil | suitable | | |
| wet maximum | suitable | | |