

GARANT Master Tap INOX machine tap HSS-E-PM, TiAIN, UNF: 12-28



Order data

Order number	138007 12-28
GTIN	4062406210205
Item class	111

Description

Version:

GARANT Master Tap INOX:

High-performance tap, specially developed for **good process reliability in stainless and acid-resistant steels** and **duplex materials.**

The 45° helix angle of the chip flutes facilitates chip formation especially in ductile austenitic CrNi steels.

- · HSS-E-PM tool material for maximum wear resistance
- The latest generation of TiALN multi-layer coating
- · Parameterised flute geometry for optimum chip formation and torsional rigidity Application:

For UNF uniform fine threads ASME – B1.1.

Thread type: UNF

Tool material: HSS E PM Standard: DIN 371 Threads per inch: 28 Thread Ø: 5.49 mm Overall length L: 80 mm Shank Ø D_s: 6 mm

Shank square \square : 4.9 mm Tapping hole \varnothing : 4.7 mm

Technical description

Overall length L	80 mm
Shank Ø D _s	6 mm
Threads per inch	28

Number of clamping slots	3		
Thread depth	13.7 mm		
Thread Ø	5.49 mm		
Thread size	12-28 UNF		
Tapping hole Ø	4.7 mm		
Standard	DIN 371		
Shank square □	4.9 mm		
Tool material	HSS E PM		
Number of cutting edges Z	3		
Thread pitch	0.907 mm		
Thread type	UNF		
Series	Master Tap		
Coating	TiAlN		
Flank angle	60 °		
Tolerance class	2BX		
Taper lead form	С		
Helix angle	45 °		
Shank	Plain shank with h9		
Through-coolant	no		
Application for type of drilling	up to 2.5×D for blind holes		
Cutting direction	right-hand		
Type of threading tool	Machine tap for dynamic machining		
Colour ring	blue		
Type of product	Тар		

User data

	Suitability	\mathbf{V}_{c}	ISO code
Aluminium (short chipping)	suitable only under restricted conditions	28 m/min	N

Steel < 750 N/mm ²	suitable only under restricted conditions	23 m/min	Р
Steel < 900 N/mm ²	suitable only under restricted conditions	23 m/min	Р
Steel < 1100 N/mm ²	suitable	12 m/min	Р
INOX < 900 N/mm ²	suitable	11 m/min	М
INOX > 900 N/mm ²	suitable	9 m/min	М
Oil	suitable		
wet maximum	suitable		