

Garant

GARANT Master Tap machine tap for wire thread inserts HSS-E-PM, AlTiX, EG-M: EG-M8



Order data

Order number	133560 EG-M8
GTIN	4062406208301
Item class	111

Description

Version:

Tap to **DIN 40435 (similar to DIN 371 / DIN 376)**.

GARANT Master Tap Universal taps, designed for use in a wide spectrum of materials with high process reliability.

- **HSS-E-PM tool material for maximum wear resistance.**
- **Reduced coefficient of friction due to the new high-performance coating.**
- **Special geometry for optimum swarf evacuation.**

Application:

For production of EG mounting thread according to metric ISO thread **DIN 8140** for **STI wire thread inserts** (Screw Thread Insert).

Note:

Please ensure without fail the correct **tapping drill Ø** (see table)!

Tool material: HSS E PM

Standard: DIN 40435

Tolerance class: 6HX mod.

Thread pitch: 1.25 mm

Overall length L: 100 mm

Shank Ø D_s: 10 mm

Shank square □: 8 mm

Tapping hole Ø: 8.4 mm

Technical description

Number of cutting edges Z	3
Thread size	M8

Standard	DIN 40435
Thread pitch	1.25 mm
Thread Ø	8 mm
Tolerance class	6HX mod.
Tapping hole Ø	8.4 mm
Shank square □	8 mm
Shank Ø D _s	10 mm
Number of clamping slots	3
Tool material	HSS E PM
Overall length L	100 mm
Thread depth	24 mm
Coating	AlTiX
Thread type	EG-M
Flank angle	60°
Taper lead form	B
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 3×D for through holes
Cutting direction	right-hand
Type of threading tool	Machine tap for dynamic machining
Colour ring	green
Series	Master Tap
Type of product	Tap

User data

	Suitability	V _c	ISO code
Alu plastics	suitable	30 m/min	N
Aluminium (short chipping)	suitable	35 m/min	N

Alu > 10% Si	suitable	20 m/min	N
Steel < 500 N/mm ²	suitable	30 m/min	P
Steel < 750 N/mm ²	suitable	30 m/min	P
Steel < 900 N/mm ²	suitable	25 m/min	P
Steel < 1100 N/mm ²	suitable	12 m/min	P
Steel < 1400 N/mm ²	suitable	8 m/min	P
INOX < 900 N/mm ²	suitable	10 m/min	M
INOX > 900 N/mm ²	suitable	8 m/min	M
GG(G)	suitable	20 m/min	K
CuZn	suitable	20 m/min	N
Uni	suitable		
Oil	suitable		
wet maximum	suitable		