Garant

GARANT Master Tap INOX machine tap HSS-E-PM, TiAIN, UNF: 7/8-14



Order data

Order number	138007 7/8-14
GTIN	4062406210281
Item class	111

Description

Version:

GARANT Master Tap INOX:

High-performance tap, specially developed for **good process reliability in stainless and acidresistant steels** and **duplex materials.**

The 45° helix angle of the chip flutes facilitates chip formation especially in ductile austenitic CrNi steels.

· HSS-E-PM tool material for maximum wear resistance

• The latest generation of TiALN multi-layer coating

 $\cdot\,$ Parameterised flute geometry for optimum chip formation and torsional rigidity Application:

For UNF uniform fine threads ASME – B1.1.

Thread type: UNF Tool material: HSS E PM Standard: DIN 374 Threads per inch: 14 Thread \emptyset : 22.23 mm Overall length L: 125 mm Shank \emptyset D_s: 18 mm Shank square \Box : 14.5 mm Tapping hole \emptyset : 20.4 mm

Technical description

Thread type	UNF
Tool material	HSS E PM

Thread size	7/8-14 UNF		
Shank square 🗆	14.5 mm		
Overall length L	125 mm		
Tapping hole Ø	20.4 mm		
Number of clamping slots	5		
Threads per inch	14		
Standard	DIN 374		
Thread depth	55.56 mm		
Thread Ø	22.23 mm		
Number of cutting edges Z	5		
Shank Ø D _s	18 mm		
Thread pitch	1.814 mm		
Series	Master Tap		
Coating	TiAIN		
Flank angle	60 °		
Tolerance class	2BX		
Taper lead form	С		
Helix angle	45 °		
Shank	Plain shank with h9		
Through-coolant	no		
Application for type of drilling	up to 2.5×D for blind holes		
Cutting direction	right-hand		
Type of threading tool	Machine tap for dynamic machining		
Colour ring	blue		
Type of product	Тар		

User data

Suitability	V _c	ISO code

Data sheet

Aluminium (short chipping)	suitable only under restricted conditions	28 m/min	Ν
Steel < 750 N/mm²	suitable only under restricted conditions	23 m/min	Ρ
Steel < 900 N/mm ²	suitable only under restricted conditions	23 m/min	Р
Steel < 1100 N/mm ²	suitable	12 m/min	Р
INOX < 900 N/mm ²	suitable	11 m/min	М
INOX > 900 N/mm ²	suitable	9 m/min	М
Oil	suitable		
wet maximum	suitable		