

**Garant**
**Combination spanner, long version, Width across flats: 32mm**

**Order data**

Order number	614600 32
GTIN	4062406220778
Item class	61A

**Description**
**Version:**

Drop-forged. With close tolerance jaw width.

With easy-grip profile shaft. Exceptional tool life and wear resistance. **Ring end deep cranked.**

**Standard:**

**DIN 3113 B / ISO 3318 / ISO 7738**

**Material:**

Chrome alloy steel; non-flaking chrome-plated, smoothed finish.

**Note:**

**HT-Drive** – the special profile. An extremely accurately fitting profile - developed for aviation and aerospace. Tools with this profile can be recognised by the **HT-Drive** symbol. **Advantages:**

- **Bolts are gripped on the flanks. – The bolts are protected. – Longer bolt life.**
- **Larger contact surfaces between bolt and tool. – Secure grip and higher torque transmission.**

**Technical description**

maximum ring height $h_{2\max}$	21 mm
Width across flats	metric
maximum jaw height $h_1$	14 mm
Width across flats	32 mm
Spanner length L	430 mm
Ring setting	10 degrees
Manufacturing process	drop forged

Material	Chrome alloy steel
Surface	chromium-plated over nickel
non-sparking	no
Ring end deep cranked	yes
Type of product	Spanner