

Garant
Double-ended ring spanner, deeply cranked, Width across flats: 24X26mm

Order data

Order number	615600 24X26
GTIN	4062406221041
Item class	61A

Description
Version:

Drop-forged. With close tolerance jaw widths.

With easy-grip profile shaft. Exceptional tool life and wear resistance. Ring ends with **HT-Drive** profile.

Standard:

DIN 838 / ISO 3318

Material:

Chrome alloy steel; non-flaking chrome-plated, smoothed finish.

Note:

HT-Drive – the particularly close-fitting profile.

Advantage

- **Bolts are gripped on the flanks.**
- **The corners are protected.**
- **Longer bolt life.**
- **Larger contact surfaces between bolt and tool.**
- **Secure grip and higher torque transmission.**

Technical description

Width across flats 2	26 mm
maximum ring $\varnothing D_2$ max	40 mm
Spanner length L	330 mm
maximum ring $\varnothing D_1$ max	36 mm
Width across flats	metric

Width across flats 1	24 mm
Ring setting	75 degrees
Manufacturing process	drop forged
Material	Chrome vanadium steel
Surface	matt chrome-plated
Ring end deep cranked	yes
open ring	no
Type of product	Spanner