

Garant**Die 6g, M: M36****Order data**

| | |
|--------------|---------------|
| Order number | 140300 M36 |
| GTIN | 4062406221188 |
| Item class | 11K |

Description**Version:**

Closed, pre-slit form. **≥ M3 with tapered lead chamfer** on both sides for easy start to the threading action and clean swarf evacuation in the direction of cutting. **1¾ turns lead chamfer.**

Cutting direction: right-hand

Tolerance class: DIN 13 6g

Pitch: 4 mm

External Ø: 65 mm

Height: 25 mm

Technical description

| | |
|-----------------|-----------|
| Height | 25 mm |
| Tolerance class | DIN 13 6g |
| External Ø | 65 mm |
| Pitch | 4 mm |
| Thread size | M36 |

| | |
|-------------------|------------|
| Thread type | M |
| Flank angle | 60 ° |
| Tool material | HSS |
| Standard | EN 22568 |
| Cutting direction | right-hand |
| Type of product | Die |

User data

| | Suitability | V _c | ISO code |
|-------------------------------|-------------------------------------------|----------------|----------|
| Aluminium (short chipping) | suitable only under restricted conditions | | |
| Steel < 500 N/mm ² | suitable | | |
| Steel < 750 N/mm ² | suitable | | |
| Oil | suitable | | |
| dry | suitable only under restricted conditions | | |