

Garant
Die, UNF: 1.1/4-12


Order data

Order number	142620 1.1/4-12
GTIN	4062406224264
Item class	11K

Description

Version:

Closed, pre-slit form; **with tapered lead chamfer on both sides** for easy start to the threading action and clean swarf evacuation in the direction of cutting. **1 $\frac{3}{4}$ turns lead chamfer.**

Application:

For UNF uniform fine threads ASME – B1.1.

Tolerance class: 2A

Threads per inch: 12

Thread \varnothing : 31.75 mm

External \varnothing : 65 mm

Height: 18 mm

Technical description

Height	18 mm
External \varnothing	65 mm
Threads per inch	12
Thread \varnothing	31.75 mm

Thread size	1.1/4-12 UNF
Cutting direction	right-hand
Thread type	UNF
Flank angle	60 °
Tool material	HSS
Standard	EN 22568
Tolerance class	2A
Type of product	Die

User data

	Suitability	V _c	ISO code
Aluminium (short chipping)	suitable only under restricted conditions		
Steel < 500 N/mm ²	suitable		
Steel < 750 N/mm ²	suitable		
Oil	suitable		
dry	suitable only under restricted conditions		