

Garant**Die 6g, M: M39****Order data**

Order number	140300 M39
GTIN	4062406221195
Item class	11K

Description**Version:**

Closed, pre-slit form. **≥ M3 with tapered lead chamfer** on both sides for easy start to the threading action and clean swarf evacuation in the direction of cutting. **1 3/4 turns lead chamfer.**

Cutting direction: right-hand

Tolerance class: DIN 13 6g

Pitch: 4 mm

External Ø: 75 mm

Height: 30 mm

Technical description

Pitch	4 mm
External Ø	75 mm
Height	30 mm
Tolerance class	DIN 13 6g
Thread size	M39

Thread type	M
Flank angle	60 °
Tool material	HSS
Standard	EN 22568
Cutting direction	right-hand
Type of product	Die

User data

	Suitability	V _c	ISO code
Aluminium (short chipping)	suitable only under restricted conditions		
Steel < 500 N/mm ²	suitable		
Steel < 750 N/mm ²	suitable		
Oil	suitable		
dry	suitable only under restricted conditions		