

Garant**Die HSS-E, MF: 5,5X0,9**

Order data

Order number	141055 5,5X0,9
GTIN	4062406223519
Item class	11K

Description

Version:Closed, pre-slit form, **with tapered lead chamfer on both sides.****2 turns lead chamfer. Lapped and nitrided, rake approx. 15°. For stainless and high-tensile steels.**

Cutting direction: right-hand

Tolerance class: DIN 13 6g

Pitch: 0.9 mm

External Ø: 20 mm

Height: 5 mm

Technical description

External Ø	20 mm
Tolerance class	DIN 13 6g
Height	5 mm
Pitch	0.9 mm
Thread size	M5.5×0.9

Thread type	MF
Flank angle	60 °
Tool material	HSS E
Standard	EN 22568
Cutting direction	right-hand
Type of product	Die

User data

	Suitability	V _c	ISO code
Steel < 500 N/mm ²	suitable		
Steel < 750 N/mm ²	suitable		
Steel < 900 N/mm ²	suitable		
Steel < 1100 N/mm ²	suitable		
Steel < 1400 N/mm ²	suitable only under restricted conditions		
INOX < 900 N/mm ²	suitable		
INOX > 900 N/mm ²	suitable only under restricted conditions		
Oil	suitable		
dry	suitable only under restricted conditions		