

Garant
Die, UNC: 1.1/4-7


Order data

Order number	142520 1.1/4-7
GTIN	4062406224189
Item class	11K

Description

Version:

Closed, pre-slit form; **with tapered lead chamfer on both sides** for easy start to the threading action and clean swarf evacuation in the direction of cutting. **1¾ turns lead chamfer.**

Application:

For UNC uniform coarse threads ASME – B1.1.

Tolerance class: 2A

Threads per inch: 7

Thread Ø: 31.75 mm

External Ø: 65 mm

Height: 25 mm

Technical description

Threads per inch	7
Height	25 mm
External Ø	65 mm
Thread Ø	31.75 mm

Thread size	1.1/4-7 UNC
Cutting direction	right-hand
Thread type	UNC
Flank angle	60 °
Tool material	HSS
Standard	EN 22568
Tolerance class	2A
Type of product	Die

User data

	Suitability	V _c	ISO code
Aluminium (short chipping)	suitable only under restricted conditions		
Steel < 500 N/mm ²	suitable		
Steel < 750 N/mm ²	suitable		
Oil	suitable		
dry	suitable only under restricted conditions		