

Garant
Die, G: G2.1/2


Order data

Order number	142050 G2.1/2
GTIN	4062406224004
Item class	11K

Description

Version:

Closed, pre-slit form; **with tapered lead chamfer on both sides** for easy start to the threading action and clean swarf evacuation in the direction of cutting. **1¾ turns lead chamfer.**

Application:

For Whitworth parallel pipe threads DIN ISO 228/1

Standard: EN 24231

Threads per inch: 11

Thread Ø: 75.18 mm

External Ø: 120 mm

Height: 22 mm

Technical description

Thread Ø	75.18 mm
Cutting direction	right-hand
Tolerance class	A
Thread size	G2,1/2

Height	22 mm
External Ø	120 mm
Threads per inch	11
Thread type	G
Flank angle	55°
Tool material	HSS
Standard	EN 24231
Type of product	Die

User data

	Suitability	V _c	ISO code
Aluminium (short chipping)	suitable only under restricted conditions		
Steel < 500 N/mm ²	suitable		
Steel < 750 N/mm ²	suitable		
Oil	suitable		
dry	suitable only under restricted conditions		