

SWISS TOOLS

## Screw-on toolholder neutral, HSK-T, Shank Ø / insert size – A dimension: 4016-80HPmm



### Order data

Order number	320080 4016-80HP
GTIN	2050002039728
Item class	36D

### Description

#### Note:

PSC clamping stud on request.

Order the suitable **HP nozzle** No. 320001 separately. Spare parts No.320610 – 320626 can be found in the spare parts list.

### Technical description

Shank Ø	40 mm
Spare part	S07
suitable indexable insert	VB.. 1604..
Overhang dimension A	80 mm
Insert size	16
Overall length	100 mm
Adapter	HSK-T
Application type	neutral
Arbor standard	ISO 12164-3
Through-coolant	yes
Shank type	Hollow shank taper

Type of product	Boring bar
-----------------	------------

## Accessories

Clamping screw No. 3 Type D07	320611 D07
High-pressure cooling nozzle (HP) Type 63	320001 63
Toggle lever No. 4 Type P06	320612 P06
Clamping screw No. 3 Type P06	320611 P06
Nozzle ring No. 5 Type D07	320613 D07
Tube pin No. 7 Type P04	320618 P04
Intermediate spacer No. 1 Type P06	320610 P06
Intermediate spacer No. 1 Type P01	320610 P01
Toggle lever No. 4 Type P04	320612 P04
Clamping screw No. 3 Type P02	320611 P02
Toggle lever No. 4 Type P05	320612 P05
Tube pin No. 7 Type P05	320618 P05
Intermediate spacer No. 1 Type P04	320610 P04
Clamping screw No. 3 Type P05	320611 P05
Toggle lever No. 4 Type P01	320612 P01
Intermediate spacer No. 1 Type P05	320610 P05
Tube pin No. 7 Type P06	320618 P06
Clamp No. 6 Type D07	320614 D07
Toggle lever No. 4 Type P02	320612 P02
Tube pin No. 7 Type P02	320618 P02
Intermediate spacer No. 1 Type P02	320610 P02
Tube pin No. 7 Type P01	320618 P01
Clamping screw No. 3 Type P01	320611 P01