

SWISS TOOLS

Screw-on toolholder right-hand, PSC, Shank \varnothing / insert size: 50/12HPmm



Order data

Order number	320310 50/12HP
GTIN	2050002039780
Item class	36D

Description

Note:

Order the suitable **HP nozzle** No. 320001 separately. Spare parts No.320610 – 320626 can be found in the spare parts list.

PSC clamping stud on request.

Technical description

Minimum pre-drill $\varnothing D_1$ min	63 mm
Spare part	S01
Insert size	12
suitable indexable insert	CC.. 1204..
Axis tip distance f	35 mm
Shank \varnothing	50 mm
Overhang dimension A	60 mm
Overall length	90 mm
Adapter	PSC
Application type	right-hand

Arbor standard	ISO 26623-1
Through-coolant	yes
Type of product	Boring bar

Accessories

High-pressure cooling nozzle (HP) Type 63	320001 63
Toggle lever No. 4 Type P04	320612 P04
Clamping screw No. 3 Type P06	320611 P06
Clamping screw No. 3 Type P05	320611 P05
Tube pin No. 7 Type P06	320618 P06
Clamping screw No. 3 Type D07	320611 D07
Toggle lever No. 4 Type P05	320612 P05
Intermediate spacer No. 1 Type P01	320610 P01
Intermediate spacer No. 1 Type P05	320610 P05
Intermediate spacer No. 1 Type P06	320610 P06
Clamping screw No. 3 Type P01	320611 P01
Intermediate spacer No. 1 Type P04	320610 P04
Tube pin No. 7 Type P02	320618 P02
Tube pin No. 7 Type P05	320618 P05
Intermediate spacer No. 1 Type P02	320610 P02
Nozzle ring No. 5 Type D07	320613 D07
Toggle lever No. 4 Type P02	320612 P02
Toggle lever No. 4 Type P01	320612 P01
Tube pin No. 7 Type P01	320618 P01
Clamping screw No. 3 Type P02	320611 P02
Clamp No. 6 Type D07	320614 D07
Toggle lever No. 4 Type P06	320612 P06
Tube pin No. 7 Type P04	320618 P04

