

Garant
Solid carbide HPC micro-drill, TiAlN, Ø DC +0.004: 0,5-Xmm

Order data

Order number	121220 0,5-X
GTIN	4062406228781
Item class	11E

Description
Version:

High performance miniature drill **with extra long flutes.**

Shank Ø 3 h6 for shrink-fit chucks.

High concentricity, precision ground for **HPC applications in steel.**

Note:

Flute length $L_c = L_2 + 1.5 \times D_c$. Delivery time: 8 working weeks.

Minimum order quantity: 15 pieces.

Items made to order for a specific customer:

Cancellation only up to a maximum of 3 working days after receipt of order acknowledgement.

Items cannot be returned.

We reserve the right to overdeliver by up to 3 items.

Technical description

Number of cutting edges Z	2
Ø range	0.5 - 0.69 mm
Standard	Manufacturer's standard
Shank Ø D_s	3 mm
Flute length L_c	7 mm
Shank tolerance	h6
Tolerance nominal Ø	0 / 0.004
Overall length L	38 mm
Coating	TiAlN

Tool material	Solid carbide
Type	N
Point angle	130 degrees
Shank	Parallel shank to h6
Through-coolant	no
Machining strategy	HPC
Semi-Standard	yes
Colour ring	without
Type of product	Jobber drill

User data

	Suitability	V _c	ISO code
Alu plastics	suitable only under restricted conditions	200 m/min	N
Aluminium (short chipping)	suitable	140 m/min	N
Alu > 10% Si	suitable only under restricted conditions	140 m/min	N
Steel < 500 N/mm ²	suitable	70 m/min	P
Steel < 750 N/mm ²	suitable	70 m/min	P
Steel < 900 N/mm ²	suitable	70 m/min	P
Steel < 1100 N/mm ²	suitable	55 m/min	P
Steel < 1400 N/mm ²	suitable	35 m/min	P
Steel < 55 HRC	suitable only under restricted conditions	25 m/min	H
INOX < 900 N/mm ²	suitable	35 m/min	M
INOX > 900 N/mm ²	suitable	30 m/min	M
Ti > 850 N/mm ²	suitable	20 m/min	S
GG(G)	suitable	90 m/min	K
CuZn	suitable	140 m/min	N

Uni	suitable
wet maximum	suitable
dry	suitable only under restricted conditions