

**MultiMaster MM 700 Max, Type: 72294661****Order data**

Order number	077804 72294661
GTIN	4014586885247
Item class	03F

Description**Version:**

Market-leading oscillating tools in three different performance classes (SuperCut, MultiMaster, MultiTalent) in a new version with **Starlock tool arbor** (improved torque transmission of up to 35 % greater rate of progression of the work).

- **Virtually unlimited application possibilities (sawing, grinding, scraping, cutting, rasping) due to the oscillating mode of movement (low generation of dust).**
- **Stepless electronic speed control for optimum working.**
- **Very high quality and stability thanks to the metal gearbox and use of ball bearings and needle bearings throughout.**
- **Optimum handling due to ergonomic design with soft-grip inlays and low weight.**

Most suitable MultiTool for rapid work progress (for interior work and renovating) with bi-metal saw blade for wood, metal and plastics. Thanks to the StarlockMax arbor, you have access to around 180 FEIN accessories from the Starlock, StarlockPlus and StarlockMax performance classes.

Supplied with:

1× E-Cut universal saw blade (44 mm), 1× plastic tool case.

Packaging: Carrying case

Manufacturer's designation: FSC 500 QSL

Power consumption: 450 W

Toolholder: Starlock Max, Starlock Plus, Starlock

Speed of oscillation: 10000 - 19500 rpm

Amplitude (oscillation movement): 2 × 2.0 degrees

Width across grinding plate head: 80 mm

Technical description

Width across grinding plate head	80 mm
Power consumption	450 W
Cable length	5 m
Speed of oscillation	10000 - 19500 rpm
Weight	1.6 kg
Manufacturer's designation	FSC 500 QSL
Toolholder	Starlock Max, Starlock Plus, Starlock
Amplitude (oscillation movement)	2 × 2.0 degrees
Power supply	Mains operated
Packaging	Carrying case
Type of product	Oscillator