



## HSS core drill Depth of cut 25 mm, Ø DC: 17mm



### Order data

|              |               |
|--------------|---------------|
| Order number | 119010 17     |
| GTIN         | 4014586612485 |
| Item class   | 03G           |

### Description

#### Version:

HSS core drill with QuickIN arbor.

**Overall length: 72 mm** for all cutter sizes.

#### Suitable for:

Quick-change system saves time with key-less tool change.

Suitable for FEIN core drill units, with adaptor also for other makes. The core drill cuts only a ring of material, saving approx. 40 % – 60 % cutting time.

#### Supplied with:

**Without** centring pin.

#### Note:

For FEIN core drill units see No. 076520/ 076524/ 076526 in section 0 – workshop accessories. The centring pin No. 119019 is required when using the core drills 119010 and 119000.

### Technical description

|                          |          |
|--------------------------|----------|
| Nominal Ø D <sub>c</sub> | 17 mm    |
| Tool material            | HSS      |
| Colour ring              | without  |
| Type of product          | Hole saw |

### User data

|                               | <b>Suitability</b>                        | <b>V<sub>c</sub></b> | <b>ISO code</b> |
|-------------------------------|---|----------------------|-----------------|
| Alu plastics                  | suitable only under restricted conditions |                      |                 |
| Aluminium (short chipping)    | suitable                                  |                      |                 |
| Alu > 10% Si                  | suitable only under restricted conditions |                      |                 |
| Steel < 500 N/mm <sup>2</sup> | suitable                                  |                      |                 |
| Steel < 750 N/mm <sup>2</sup> | suitable                                  |                      |                 |
| Steel < 900 N/mm <sup>2</sup> | suitable only under restricted conditions |                      |                 |
| INOX < 900 N/mm <sup>2</sup>  | suitable only under restricted conditions |                      |                 |
| GG(G)                         | suitable only under restricted conditions |                      |                 |
| Oil                           | suitable                                  |                      |                 |
| wet maximum                   | suitable                                  |                      |                 |