


Solid carbide jobber drill, TiN, Ø DC h7: 4,3mm

Order data

| | |
|--------------|---------------|
| Order number | 122301 4,3 |
| GTIN | 4045197042484 |
| Item class | 12E |

Description
Version:
Similar to DIN 338.

Nominal Ø and shank Ø equal.

TiN coating.

Note:

Flute length $L_c = L_2 + 1.5 \times D_c$.

Non slip clamping in drill chuck No. 341050 with diamond coated jaws.

Technical description

| | |
|---|---------------|
| Number of cutting edges Z | 2 |
| Feed f in steel < 1100 N/mm ² | 0.08 mm/rev. |
| Shank tolerance | h7 |
| Nominal Ø D _c | 4.3 mm |
| Flute length L _c | 47 mm |
| Tolerance nominal Ø | h7 |
| Shank Ø D _s | 4.3 mm |
| Overall length L | 80 mm |
| Standard | DIN 338 |
| recommended maximum drilling depth L ₂ | 40.6 mm |
| Coating | TiN |
| Tool material | Solid carbide |

| | |
|-----------------|----------------------|
| Type | N |
| Point angle | 118 degrees |
| Helix angle | 30 degrees |
| Shank | Parallel shank to h7 |
| Through-coolant | no |
| Colour ring | without |
| Type of product | Jobber drill |

User data

| | Suitability | V _c | ISO code |
|--------------------------------|---|----------------|----------|
| Alu plastics | suitable only under restricted conditions | 230 m/min | N |
| Aluminium (short chipping) | suitable | 160 m/min | N |
| Alu > 10% Si | suitable | 160 m/min | N |
| Steel < 500 N/mm ² | suitable | 80 m/min | P |
| Steel < 750 N/mm ² | suitable | 80 m/min | P |
| Steel < 900 N/mm ² | suitable | 70 m/min | P |
| Steel < 1100 N/mm ² | suitable | 50 m/min | P |
| Steel < 1400 N/mm ² | suitable | 30 m/min | P |
| INOX < 900 N/mm ² | suitable only under restricted conditions | 30 m/min | M |
| INOX > 900 N/mm ² | suitable only under restricted conditions | 25 m/min | M |
| Ti > 850 N/mm ² | suitable | 20 m/min | S |
| GG(G) | suitable | 85 m/min | K |
| CuZn | suitable | 160 m/min | N |
| Uni | suitable | | |
| Oil | suitable | | |
| wet maximum | suitable | | |

dry

suitable only under
restricted conditions