



Straight die grinder, Type: GGS28CE



Order data

Order number	077265 GGS28CE
GTIN	3165140584814
Item class	03C

Description

Version:

Handy compact straight die grinder for versatile grinding operations.

- **Constant-speed electronics maintain constant speed even at high loads.**
- **New clamping system for zero-play fixing of the grinding points for precise working.**
- **Soft start and Kick-Back stop: If the machine senses a jam, it switches off immediately.**
- **Switch-off carbon brushes for high protection of the motor.**
- **Long working life thanks to direct cooling and double sealed ball bearings.**
- **6-speed pre-selection to cater for different materials.**
- **With short spindle neck, permits stationary use (43 mm clamp).**

Supplied with:

Supplied with 6 mm collet, 2 chuck wrenches AF 19.

Technical description

maximum vibration to EN	8.0 m/s ²
Power consumption	650 W
electronic speed pre-selection	yes
Manufacturer's designation	GGs 28 CE
Weight	1.4 kg
Speed range	10000 - 28000 min ⁻¹
maximum collet Ø	6 mm

Power supply	Mains operated
Type of product	Straight die grinder