



Straight die grinder, Type: GGS28LCE



Order data

Order number	077265 GGS28LCE
GTIN	3165140584821
Item class	03C

Description

Version:

Handy compact straight die grinder for versatile grinding operations.

- **Constant-speed electronics maintain constant speed even at high loads.**
- **New clamping system for zero-play fixing of the grinding points for precise working.**
- **Soft start and Kick-Back stop: If the machine senses a jam, it switches off immediately.**
- **Switch-off carbon brushes for high protection of the motor.**
- **Long working life thanks to direct cooling and double sealed ball bearings.**
- **6-speed pre-selection to cater for different materials.**
- **With long slim grinding spindle – particularly suitable for use in inaccessible places.**

Supplied with:

Supplied with 6 mm collet, 2 chuck wrenches AF 19.

Technical description

Power consumption	650 W
Manufacturer's designation	GGs 28 LCE
Weight	1.6 kg
electronic speed pre-selection	yes
maximum vibration to EN	14 m/s ²
Speed range	10000 - 28000 min ⁻¹
maximum collet Ø	6 mm
Power supply	Mains operated

Type of product

Straight die grinder