



## Straight die grinder, Type: GGS8CE



### Order data

Order number	077265 GGS8CE
GTIN	3165140584852
Item class	03C

### Description

#### Version:

Handy compact straight die grinder for versatile grinding operations.

- **Constant-speed electronics maintain constant speed even at high loads.**
- **New clamping system for zero-play fixing of the grinding points for precise working.**
- **Soft start and Kick-Back stop: If the machine senses a jam, it switches off immediately.**
- **Switch-off carbon brushes for high protection of the motor.**
- **Long working life thanks to direct cooling and double sealed ball bearings.**
- **6-speed pre-selection to cater for different materials.**
- **With long slim grinding spindle – particularly suitable for use in inaccessible places.**
- **High-torque 750 Watt motor for a high rate of progression of the work.**
- **Reduced speed, suitable also for grinding stainless steel.**

#### Supplied with:

Including collet 6 mm, 2 single open ended spanner AF 13 and AF 19.

### Technical description

electronic speed pre-selection	yes
maximum vibration to EN	< 2.5 m/s <sup>2</sup>
Weight	1.7 kg
Manufacturer's designation	GG8 8 CE
Power consumption	750 W
Speed range	2500 - 8000 min <sup>-1</sup>

maximum collet Ø	6 mm
Power supply	Mains operated
Type of product	Straight die grinder