



Cordless impact wrench, Type: M18FIW12



Order data

Order number	074010 M18FIW12
GTIN	4002395810550
Item class	03L

Description

Version:

Robust and **powerful FUEL™ cordless impact wrench** with **brushless POWERSTATE™ EC motor** for long motor service life and high energy efficiency. Sturdy **metal gearbox casing** and ergonomic **central handle with soft-grip coating**. Stage of charge display, LED illumination of the working area. Reversible, with electronic speed control. **REDLINK PLUS™ electronics** – for unique power management:

- **With system communication between the drive machine and battery.**
- **With overload protection for longer working life of the battery, motor, and gearbox.**

DRIVE CONTROL™ permits quick switching between the 4 available settings with different speeds and torques. **18 V / 5.0 Ah compact cordless impact driver** with only 151 mm overall length. Stage 4 - for intelligent working, the device switches off automatically in seconds as soon as the screw fastening is created.

Standard:

Robust and **powerful FUEL™ cordless impact screwdriver** with **brushless POWERSTATE™ EC motor** for long motor service life and high energy efficiency.

Supplied with:

Supplied with 2× Li-ion batteries, charger, HD box, belt clip.

Attention:

German version. Order free UK adapter plug No. 08 1172_GB.

Note:

See No. 073808 ff. for suitable spare batteries and accessories.

Packaging: Modular case (HD=Heavy Duty)

suitable battery - supplier / battery type / voltage: Milwaukee type B 18 V

Manufacturer's designation: M18 FIWF12

Number of rechargeable batteries contained: 2

Type of rechargeable battery: Lithium-ion

Battery capacity: 5 A·h

Battery voltage: 18 V

maximum torque 1st step: 40 N·m

Technical description

Battery voltage	18 V
Tool arbor size	1/2 inch
Number of impacts 2nd stage	0 - 3000 rpm
maximum torque 1st step	40 N·m
maximum torque 2nd step	120 N·m
Number of impacts 1st stage	0 - 2500 rpm
Battery capacity	5 A·h
Manufacturer's designation	M18 FIWF12
Type	M18 FIWF12
maximum vibration to EN	14.3 m/s ²
Packaging	Modular case (HD=Heavy Duty)
suitable battery - supplier / battery type / voltage	Milwaukee type B 18 V
Number of impacts 3rd stage	0 - 3100 rpm
maximum screw Ø (8.8 - 12.9)	M18
maximum torque 3rd step	300 N·m
typical application	Strong
Weight	1.9 kg
Tool arbor drive profile	External square drive
Number of impacts 4th setting	0 - 3000 rpm
maximum torque 4th setting	120 N·m
Number of rechargeable batteries contained	2

Type of rechargeable battery	Lithium-ion
------------------------------	-------------

Accessories

Li-ion system M18B5 Rechargeable battery type, battery voltage MB18 V	073816 MB18
---	-------------

Battery charger Type M1218C	073840 M1218C
-----------------------------	---------------

Battery charger Type M1218FC	073840 M1218FC
------------------------------	----------------